

# Power Outlets - Surface



R32U	R32U	R32U	(4) 5-20R2GFCI	7310	R32U 5-20R2	R32U 5-20R2
<b>A</b> <b>U013C</b>	<b>M</b> <b>U132CTL</b>	<b>B</b> <b>U013F</b>	<b>C</b> <b>U014C010</b>	<b>D</b> <b>U023</b>	<b>E</b> <b>U041</b>	<b>F</b> <b>U041C</b>

R32U 5-20R2	R32U 5-20R2GFCI	10-50R	10-50R	10-50R 5-20R2	14-50R
<b>G</b> <b>U041F</b>	<b>H</b> <b>U041010</b>	<b>I</b> <b>U050</b>	<b>J</b> <b>U050C</b>	<b>K</b> <b>U051F</b>	<b>L</b> <b>U054</b>

Temp Power /  
Power Outlets

## Surface - Unmetered

FIG.	UL	MODEL NUMBER	RECEPTACLES	CIRCUIT PROTECTION	AMP	VOLTS	WIRE RANGE*	CABINET SIZE	HUB OPENING	LOAD & NEUTRAL BAR	UNIT WT.	STD. PKG.
A	Y	U013C	R32U	CB130	30	120	A	6 X 9	Y	LC31N3	7	4
M	Y	U132CTL	R32U	CB130 SPACE (2) CB120	100	120/240	V	9 X 17	Y	LC33N1T	11	1
B	Y	U013F	R32U	F 3	30	120	F	5 X 7	Y		4.5	4
C	Y	U014C010 <sup>1</sup>	(4) 5 20R2GFC	(4) CB120 SPACE CB120	100	120/240	U	9 X 17	Y	LC55N1	28	1
D	N	U023	7310		20	120/240	F	5 X 7	Y		4.5	4
E	Y	U041	R32U 5 20R2		30	120/240	E	6 X 9	Y		6	4
F	Y	U041C	R32U 5 20R2	CB130 CB120 SPACE CB120	70	120/240	K	6 X 14	Y	LC33N7	10	4
G	Y	U041F	R32U 5 20R2	F 3 F 2	30	120/240	E	6 X 9	Y		7	4
H	Y	U041010	R32U 5 20R2GFC		30	120/240	J	6 X 9	Y		9	4
I	N	U050	10 50R		50	120/240	G	5 X 7	Y		4.5	4
J	N	U050C	10 50R	CB250 SPACE CB120	70	120/240	O	6 X 14	Y	LC33N7	10	4
K	N	U051F	10 50R 5 20R2	F 2	50	120/240	K	6 X 14	Y	FR66	10	4
L	Y	U054	14 50R		50	120/240	G	5 X 7	Y		5	4

<sup>1</sup> Earth Burial Model U014CP6010

\* Wire Range Table on pages 54-55

## Technical Data

MODEL NUMBER	REPLACEMENT PARTS		CABINET SIZE	ENCLOSURE STYLE page 65	CABINET DIMENSIONS			KNOCKOUT FIGURE page 65
	METER SOCKET	POST LUGS			HEIGHT	WIDTH	DEPTH	
					A	B	C	
M058C	MSM100930		9 X 30	B	30"	9 3/4"	5 3/16"	2
M058CB6	MSM100P9	LT100B350	9PT		See page 66			
M132CB6	MSM100P9	LT100B350	9PT		See page 66			
M132CP6	MSM100P9	LT100S250	9PT		See page 66			
M358CP6	MSM100P9	LT100S250	9PT		See page 66			
R058C	MSR100930		9 X 30	B	30"	9 3/4"	5 3/16"	2
R058CB6	MSR100P9	LT100B350	9PT		See page 66			
R058CP6	MSR100P9	LT100S250	9PT		See page 66			
U002C			9 X 17	A	17 3/8"	9 3/4"	5 3/16"	2
U004F			14 X 21	A	21 3/8"	14 3/4"	6 7/16"	3
U004CTL010			9 X 17	A	17 3/8"	9 3/4"	5 3/16"	2
U010			5 X 7	A	7 1/8"	5 3/4"	5 3/16"	4
U010010/U010010GRP			5 X 7	A	7 1/8"	5 3/4"	5 3/16"	4
U010C			6 X 9	A	9 1/8"	7 1/4"	5 3/16"	1
U010F			5 X 7	A	7 1/8"	5 3/4"	5 3/16"	4
U010H			5 X 7	A	7 1/8"	5 3/4"	5 3/16"	4
U010S010/U010S010GRP			5 X 7	A	7 1/8"	5 3/4"	5 3/16"	4
U011			5 X 7	A	7 1/8"	5 3/4"	5 3/16"	4
U011010			5 X 7	A	7 1/8"	5 3/4"	5 3/16"	4
U011F			6 X 9	A	9 1/8"	7 1/4"	5 3/16"	1
U012010			5 X 7	A	7 1/8"	5 3/4"	5 3/16"	4
U012010GRP			5 X 7	A	7 1/8"	5 3/4"	5 3/16"	4
U013			5 X 7	A	7 1/8"	5 3/4"	5 3/16"	4
U013C			6 X 9	A	9 1/8"	7 1/4"	5 3/16"	1
U013F			5 X 7	A	7 1/8"	5 3/4"	5 3/16"	4
U014C010			9 X 17	A	17"	9 1/2"	5 1/5"	2
U014CP6010			9PT		See page 66			
U023			5 X 7	A	7 1/8"	5 3/4"	5 3/16"	4
U025S			5 X 7	A	7 1/8"	5 3/4"	5 3/16"	4
U041/U041010			6 X 9	A	9 1/8"	7 1/4"	5 3/16"	1
U041C			6 X 14	A	14 3/8"	7 1/4"	5 3/16"	1
U041F			6 X 9	A	9 1/8"	7 1/4"	5 3/16"	1
U050			5 X 7	A	7 1/8"	5 3/4"	5 3/16"	4
U050C			6 X 14	A	14 3/8"	7 1/4"	5 3/16"	1
U051F			6 X 14	A	14 3/8"	7 1/4"	5 3/16"	1
U054			5 X 7	A	7 1/8"	5 3/4"	5 3/16"	4
U054F			6 X 14	A	14 3/8"	7 1/4"	5 3/16"	1
U055010			6 X 9	A	9 1/8"	7 1/4"	5 3/16"	1
U055F			6 X 14	A	14 3/8"	7 1/4"	5 3/16"	1
U058C			9 X 17	A	17 3/8"	9 1/4"	5 3/16"	2
U058CB6		LT100B250	9PT		See page 66			
U058CP6		LT100S250	9PT		See page 66			
U061C			6 X 14	A	14 3/8"	7 1/4"	5 3/16"	1